

VariMax™ Operation Guide



- The VariMax system offers a wide range of speeds for the user.
- The VariMax control can be set to a continuous high speed or low speed, or in between.
- The VariMax also has a Wave Mode that automatically ramps from high speed to low speed, then back up to high speed. It then repeats.

Operation

- The LED is lit when the pump is on.
- The LED is not lit when the pump is off.

Manual Speed Control

- Press the ON/OFF/WAVE button
- Press SPEED DOWN for each incremental change in speed
- Press SPEED UP for each incremental change in speed

Wave Control

- Press and hold the ON/OFF/WAVE button